

同步带压板 过压防止型

成本
经济型产品

库存产品

交期缩短


大批量
订购
bulk order

过压防止型



代号	类型	M 材质	S 表面处理	A 附件
SMP	过压防止型	铝合金	本色阳极氧化	内六角螺钉

产品特点: 通过上下金属件面与面接触可防止皮带过紧。



订购编号示例

① 代号 - ② 齿形 ③ 公称宽度
SMP - XL025

过压防止型																
① 代号	② 齿形	③ 公称宽度	宽度(mm)	A	B	T ₁	T ₂	T ₃	h	L	P	M	d	螺栓规格	安装孔数	
SMP	XL	025	6.4	66	24	6	4.5	2.1	1.3	56	13	M4	4.5	M4-10	6	
		037	9.5		26						16					
		050	12.7		30						20					
	L	050	12.7	124	32	8	5.5	3.33	2.05	111	21	M5	5.5	M5-12	8	
		075	19.1		38						27					
		100	25.4		46						34					
	H	075	19.1	165	38	10	6.5	4.15	2.55	147	27	M5	5.5	M5-14	8	
		100	25.4		46						34					
		150	38.1		58						46					
	T5	100	10	65	26	6	4.5	2.2	1.4	51	17	M4	4.5	M4-10	6	
		150	15		32						22					
		200	20		38						27					
	T10	250	25	130	43	8	6.5	4.3	2.7	111	32	M5	5.5	M5-12	8	
		150	15		34						23					
		200	20		40						28					
	S3M	250	25	39	44	4	3.5	1.94	1.25	31	33	M3	3.4	M3-6	6	
		300	30		50						38					
		400	40		60						48					
	S5M	500	50	65	70	6	5.5	3.14	2	51	58	M4	4.5	M4-10	6	
		150	15		34						23					
		250	25		42						32					
	S8M	150	15	104	34	8	6.5	4.72	3	84	23	M5	5.5	M5-12	8	
		250	25		44						33					
		300	30		50						38					
S8M	400	40	104	60	8	6.5	4.72	3	84	48	M5	5.5	M5-12	8		
	300	30		50						38						

- ▲ 本产品的的设计适用于聚氨酯同步带。与其它同步带啮合时，请确认同步带的背厚及产品尺寸后再使用。
- ▲ 齿形依据橡胶同步带和聚氨酯同步带。
- ▲ A 尺寸为 6 齿（金属件）啮合设定。

D4
同步带