


# 悬臂销




★ 产品特点：侧板外螺纹安装，零件侧外螺纹紧固，安装方便。

## ■ 六角型



①代号		M材质	S表面处理
螺纹长度固定型	螺纹长度选择型		
CSPBHG	CSPBHGL	45#	四氧化三铁保护膜
CSPEHG	CSPEHGL		无电解镀锌
CSPNHG	CSPNHGL	SUS304	-



视角标准：第一视角




①代号 - ②No - ③B - ④L - ⑤H - ⑥M  
 CSPBHGL - 12 - B6 - L16 - H12 - M10

①代号	②No	轴径		指定单位1mm			⑥M(粗牙)	W	E(参考尺寸)	M	
		D	公差g6	③B	④L	⑤H					
(螺纹长度固定型) CSPBHG CSPEHG CSPNHG	3	3	-0.002 -0.008	2 ~ 30	3 ~ 50	3 ~ 6	3	6	6.9	M 3	
	4	4				4 ~ 8	3 4			M 4	
	5	5	-0.004 -0.012				5 ~ 10	3 4 5	7	8.1	M 5
	6	6					6 ~ 12	4 5 6	8	9.2	M 6
	8	8	-0.005		5 ~ 75	5 6 8	10	11.5	M 8		
	10	10	-0.014			10 ~ 20	6 8 10	13	15	M10	
	12	12		2 ~ 60			6 8 10 12	14	16.2		
	13	13						17	19.6		
	15	15	-0.006				12 ~ 24				
	16	16	-0.017					8 10 12 -15	19	21.9	M12
(螺纹长度选择型) CSPBHGL CSPEHGL CSPNHGL	17	17									
	18	18									
	20	20		10 ~ 75						M20	
	20A	20A					10 12 -15 16 20	24	27.7	M16	
	22	22								M20	
	22A	22A								M16	
	25	25	-0.007 -0.02	4 ~ 60		20 ~ 40				M20	
	25A	25A					10 12 -15 16 20 24 -25	27	31.2	M16	
	30	30								M20	
	30A	30A					12 -15 16 20 24 -25 30	32	36.9	M16	

- ▲ 有些尺寸可能带中心孔。
- ▲ 有关外螺纹的退刀槽尺寸参见外螺纹退刀槽加工尺寸表。
- ▲ 仅螺纹长度选择型可指定H。

螺纹直径(MD)	粗牙螺纹		
	T	R	K
3			2.1~2.4
4	1.2~1.5	0.2~0.3	2.9~3.2
5			3.9~4.1
6			4.3~4.9
8	1.5~2.5	0.2~0.6	6.3~6.6
10			8.1~8.3
12			9.8~10.1
16	1.5~3.0	0.2~1.0	13.6~13.8
20	1.5~4.0		17.0~17.2
24			20.2~20.7
30	2.5~5.0	0.2~1.5	26.0~26.2



交货期 **10** 工作日

- ▲ 常州发货
- ▲ 部分产品型号 12 天发货，请以报价为准
- ▲ 遇特殊期间交期有变更

	标准订单	特殊订单
数量	1~100	101~
交货期	10 个工作日	现询

▲ 遇到特殊期间，货期会有变更，详情请见官网通知。

