


重载型支脚



★ 产品特点：底座由增强尼龙 (PA6) 制成，耐撞击和敲打，耐腐蚀。



①代号	底盘		螺杆	
	④材质	④材质	⑤表面处理	
SFBCQL	增强尼龙(PA6)	45#	镀铬	
SFSQL		SUS304	无	

SFBCQL
SFSQL

视角标准：第一视角

G2 支脚



①代号 - ②底径 - ③螺纹直径 - ④螺纹长度
SFBCQL - D80 - M16 - L150

型号		主要尺寸									承载(kg)	参考重量(kg/pcs)
①代号	②D	③M	④L	E	E ₁	D ₁	H	B	d	F		
钢 SFBCQL 不锈钢 SFSQL	80	M16	50	24	19	60	39			13	1000	0.17
			100									0.19
			150									0.21
		M20	50	30	24		42	29	9	16		0.18
			100				0.22					
			150				0.23					
	M24	50	36		45			19	0.27			
		100			0.3							
		150			0.32							
	100	M16	50	24	19	75	46			13	1400	0.37
			100									0.39
			150									0.41
M20		50	30	24	49		36	11	16	0.49		
		100			0.52							
		150			0.55							
M24	50	36		52			19	0.61				
	100			0.64								
	150			0.69								

▲ 承载与参考重量仅供参考。
▲ 需搭配膨胀螺栓使用。



数量分类	小单	中大单	大单
数量	1~50	51~100	101~
交货期	通常	7 工作日	现询



数量	1-9	10~
价格	100%	另行报价

