




标准型/进口型 深沟球轴承



★ 产品特点：两侧的铁盖具有较好的防尘性



①代号	类型	后置代号	轴承材质	
			GB	JIS
BRG	标准型	ZZ: 双面带防尘盖	GCr15	SUJ2
SBRG			2Gr13	SUS420
HQ-BRG	进口型		GCr15	SUJ2
HQ-SBRG			9Cr18Mo	SUS440C



型号
HQ-BRG-6700ZZ

①代号	②公称规格	d	D	B	r (min)	基本额定载荷				最大允许转速 (rpm)	安装尺寸				重量 g (参考)
						标准		进口			Ds		dh (max)	R (max)	
						动载荷/KN	静载荷/KN	动载荷/KN	静载荷/KN		min	max			
6700ZZ		15	4	0.2	0.85	0.43	1	0.62	15000	10.4	11.21	14.2	0.2	2	
6800ZZ		19	5		1.52	0.64	1.72	0.84	34000		12.5	17		5	
6900ZZ		22	6	0.3	2.5	1.07	2.7	1.27	32000	12	13	20	0.3	9	
6000ZZ		26	8		4.35	1.76	4.55	1.97	30000		13.5	24		19	
6200ZZ		30	9		4.9	2.19	5.1	2.39	24000	14	16	26	0.6	32	
6300ZZ		35	11	0.6	7.9	3.25	8.1	3.45	21000		16.5	31		52	
6701ZZ		18	4	0.2	0.92	0.53	1.12	0.73	13000	12.4	13.86	16.7	0.2	3	
6801ZZ		21	5		1.72	0.84	1.92	1.04	32000		14.5	19		6	
6901ZZ		24	6	0.3	2.69	1.26	2.89	1.46	30000	14	15	22	0.3	11	
6001ZZ		28	8		4.9	2.19	5.1	2.37	27000		16	26		21	
6201ZZ		32	10	0.6	6.1	2.75	6.8	3.05	22000	16	17	28	0.6	37	
6301ZZ		37	12	1	9.5	4	9.7	4.2	19000	17	18	32	1	60	
6702ZZ		21	4	0.2	0.93	0.58	1.13	0.78	11000	15.4	16.86	19.7	0.2	4	
6802ZZ		24	5		1.88	1.06	2.07	1.26	27000		22			7	
6902ZZ		28	7	0.3	3.65	2	4.35	2.26	26000	17	17.5	26	0.3	16	
6002ZZ		32	9		5.4	2.63	5.6	2.83	23000		19	30		30	
6202ZZ		35	11	0.6	7.45	3.6	7.65	3.75	19000	19	20	31	0.6	45	
6302ZZ		42	13	1	11.2	5.25	11.4	5.45	17000	20	22.5	37	1	83	
6703ZZ		23	4	0.2	1	0.65	1.2	0.85	9500	17.4	18.86	21.1	0.2	4	
6803ZZ		26	5		2.23	1.46	2.63	1.57	25000		19.5	24		8	
6903ZZ		30	7	0.3	4.4	2.38	4.6	2.55	23000	19	20	28	0.3	18	
6003ZZ		35	10		5.8	3.05	6	3.25	20000		21	33		39	
6203ZZ		40	12	0.6	9.35	4.6	9.55	4.8	17000	21	23	36	0.6	66	
6303ZZ		47	14	1	13.4	6.45	13.6	6.65	15000	22	25.5	42	1	113	
6704ZZ		27	4	0.2	1.4	0.72	1.6	0.92	8500	20.4	22.36	25.5	0.2	6	
6804ZZ		32	7		3.8	2.27	4	2.47	20000		22.5	30		19	
6904ZZ		37	9	0.3	6.2	3.5	6.4	3.7	19000	22	24	35	0.3	36	
6004ZZ		42	12	0.6	9.2	4.85	9.4	5	17000	24	26	38	0.6	69	
6204ZZ		47	14	1	12.6	6.4	12.8	6.6	14000	25		42		106	
6304ZZ		52	15	1.1	15.7	7.7	15.9	7.9	13000	26.5	28	45.5	1	145	
6805ZZ		37	7	0.3	4.3	2.95	4.5	3.15	18000	27		35		22	
6905ZZ		42	9		6.85	4.35	7.05	4.55	16000		29	40	0.3	42	
6005ZZ		47	12	0.6	9.9	5.65	10.1	5.85	15000	29	30.5	43	0.6	80	
6205ZZ		52	15	1	13.8	7.65	14	7.85	12000	30	32	47		128	
6305ZZ		62	17	1.1	20.4	11	20.6	11.2	11000	31.5	36	55.5	1	235	
6806ZZ		42	7	0.3	4.5	3.45	4.7	3.65	15000			55.5		235	
6906ZZ		47	9		7.25	5	7.05	4.8	14000	32	33	40		26	
6006ZZ		55	13		13.2	8.3	13	8.1	12000		34	45	0.3	48	
6206ZZ		62	16	1	19.5	11.3	19.3	11.1	10000		37	50		116	
6306ZZ		72	19	1.1	26.5	14.5	26.7	15	9200	36.5	37.5	45.5	1	199	
6807ZZ		47	7	0.3	4.7	4.05	4.9	4.1	13000	37	38	45	0.3	29	
6907ZZ		55	10	0.6	9.55	6.85	10.6	7.25	12000	39	40	51	0.6	74	
6007ZZ		62	14	1	15.8	10.1	16	10.3	11000	40	42	57		155	
6207ZZ		72	17	1.1	25.5	15.1	25.7	15.3	9000	41.5	45	65.5	1	288	
6307ZZ		80	21	1.5	33.3	19	33.5	19.2	8400	43	47	72	1.5	469	
6808ZZ		52	7	0.3	5.1	4.4	6.35	5.55	12000	42	43	50	0.3	33	
6908ZZ		62	12	0.6	12.2	8.9	13.7	10	11000	44	45	58	0.6	110	
6008ZZ		68	15	1	16.6	11.3	16.8	11.5	9500	45	47	63		190	
6208ZZ		80	18	1.1	28.9	17.6	29.1	17.9	8200	46.5	51	73.5	1	366	
6308ZZ		90	23	1.5	40.3	23.8	40.5	24	7500	48	53	82	1.5	636	
6809ZZ		58	7	0.3	6.18	5.38	6.6	6.15	11000	47	47.5	56	0.3	38	
6909ZZ		68	12	0.6	13.9	10.6	14.1	10.9	9500	49	50	64	0.6	126	
6009ZZ		75	16	1	20.7	15	20.9	15.2	8800	50	53.5	70		241	
6209ZZ		85	19	1.1	31.3	20.2	31.5	20.4	7500	51.5	55.5	78.5	1	420	
6309ZZ		100	25	1.5	52.8	31.8	53	32	6700	53	61.5	92	1.5	829	
6810ZZ		65	7	0.3	6.2	6.09	6.4	6.2	9500	52	52.5	63	0.3	50	
6910ZZ		72	12		14.3	11.5	14.5	11.7	9000	54	55	68	0.6	135	
6010ZZ		80	16	1	21.6	16.4	21.8	16.6	8300	55	57.5	75		261	
6210ZZ		90	20	1.1	34.8	23	35	23.2	7000	56.5	60	83.5	1	454	
6310ZZ		110	27	2	61.8	38	62	38.5	6000	59	68	101	2	1006	

C2 轴承无锁紧螺母

▲ 1kgf=9.8N
▲ 不承诺此产品品牌
▲ 更多规格请咨询客服

交货期 **4** 天发货