

圆形截面圆柱形拉伸弹簧

中重载型

■中重载型




① 代号	类型	④ 材质
ESEJP	中重载型	SWP-A

J2
弹
簧

订购编号示例

① 代号	-	② D	-	③ L	-
ESEJP	-	D3	-	L10	-



① 代号	② D	③ L	d	动态负载时		(初拉力) (N)	弹簧系数 (N/mm)
				工作行程 S (mm)	工作极限载荷 (N)		
ESEJP	3	10	0.45	2.2	6.47	1.57	2.26
		15		4.5			1.08
		20		6.7			0.74
		25		9.1			0.54
		30		11.4			0.43
	4	15	0.55	4.5	8.43	1.86	1.47
		20		7.1			0.93
		25		10.0			0.66
		30		12.6			0.52
		35		15.2			0.43
	5	15	0.7	3.9	14.71	2.45	3.14
		20		6.9			1.77
		25		9.6			1.28
		30		12.5			0.98
		35		15.6			0.78
	6	20	0.9	3.9	23.54	5.88	4.51
		25		6.0			2.94
		30		7.8			2.26
		35		10.0			1.77
		40		12.0			1.47
		45		13.8			1.28
		50		16.4			1.08
		55		18.0			0.98
		60		20.0			0.88
		8		25			1.1
	30		8.3	2.94			
	35		10.9	2.26			
	40		13.2	1.86			
	45		15.6	1.57			
	50		18.5	1.32			
55	21.7		1.13				
60	23.8		1.03				
10	30	1.4	6.5	49.03	12.75	5.58	
	35		8.7			4.17	
	40		10.7			3.39	
	45		12.9			2.81	
	50		15.2			2.39	
55	17.2	2.11					

① 代号	② D	③ L	d	动态负载时		(初拉力) (N)	弹簧系数 (N/mm)
				工作行程 S (mm)	工作极限载荷 (N)		
ESEJP	10	60	1.4	19.5	49.03	12.75	1.86
		70		23.1			1.57
		80		27.4			1.32
		90		32.1			1.13
		100		46.2			0.79
	12	35	1.8	5.0	83.36	23.54	12.00
		40		7.0			8.55
		45		9.0			6.65
		50		11.0			5.44
		55		13.0			4.60
		60		14.5			4.13
		70		17.8			3.36
		80		21.3			2.81
		90		24.5			2.44
		100		27.5			2.18

▲初拉力、弹簧系数为参考值。载荷 (kgf) = 载荷 N × 0.101972