


弹簧柱塞

带法兰型




	主体			球头		弹簧	可使用温度
	M材质	H硬度	S表面处理	M材质	H硬度	M材质	
POA	45#	29 ~ 35HRC	发黑	SUS440C	55HRC ~	SUS631J1	-30 ~ 80°C
POB	SUS303	-	-	-	-	-	-30 ~ 260°C




1 代号 - 2 M
POA - M5

1 代号	2 M(粗牙螺纹)	D	L	S	d	a	许用载荷(N)			
							POA		POB	
							min.	max.	min.	max.
POA POB	5	7	5	0.8	3	0.8	0.6	5.6	1.3	6.4
	6	8	6	1	4	1	2.8	6.3	2.7	8
	8	10	7	1.6	5	1.5	2.9	9.6	1.3	10.2
	10	12	9	1.9	6.35		6.4	11.7	6.1	17.2
	12	14	11.5	2.4	7.94	9	15	2.1	18.8	
	16	18	16	3.2	9.53	2	9.9	21.5	13	25.5

内六角短型



	主体	球头		弹簧	调整环	可使用温度
	M材质	M材质	H硬度	M材质	M材质	
PPB	SUS304	SUS440C	59 ~ 66HRC	SUS304-WPB	SUS304	-30 ~ 80°C



1 代号 - 2 M
PPB - M3

1 代号	2 M(粗牙螺纹)	d	S	L	L ₁	B	许用载荷(N)	
							min.	max.
PPB	3	2	0.5	5	1	1.5	1	2
	4	2.5	0.8	6	1.2	2	1.1	3.7
	5	3		8	1.7	2.5	2.2	5.9
	6	4	1	9	1.8	3	4.6	8.7
	8	5	1.2	10	1.8	4	7.5	11.9