


# 国产拖链/接头/分隔片




## ■ 拖链



代码	类型	打开方式	横梁	材材质	颜色	允许温度	阻燃等级	附件
DGT25L	25系列拖链	内外径打开	桥式	增强尼龙6	黑色	-20℃~80℃	UL94-HB	接头
DGU25L			全封闭式					

▲ 本系列拖链标准型号包含一套接头(移动端、固定端各一个)。  
 ▲ 本系列拖链不包含分隔片, 分隔片需要单独购买。

主体尺寸图



M1  
拖链



①代号 - ②内宽B<sub>1</sub> - ③弯曲半径R - ④链节数N  
 DGT25L - 50 - R75 - N20

①代号	②内宽B <sub>1</sub>	③弯曲半径R	④链节数N	⑤接头	安装尺寸			实际安装高度H <sub>F</sub>	外宽B <sub>2</sub>	节距P	最大电缆直径(mm)	最大架空负载(kg/m)	最大允许行程(m)	最大垂直悬挂(m)	重量 kg/m		
					H	D	K								DGT25L	DGU25L	
DGT25L DGU25L	25	(40)	1~	D25FJ-25	120	106	230	160	42								
		150			121	276	190										
		190			141	368	230										
		240			166	414	280										
		290			191	506	330										
		340			216	598	380										
	38	(40)	1~	D25FJ-38	120	106	230	160	55								
		150			121	276	190										
		190			141	368	230										
		240			166	414	280										
		290			191	506	330										
		340			216	598	380										
	50	(40)	1~	D25FJ-50	120	106	230	160	67	46	22	1.3	70.0	30			
		150			121	276	190										
		190			141	368	230										
		240			166	414	280										
		290			191	506	330										
		340			216	598	380										
	57	(40)	1~	D25FJ-57	120	106	230	160	74								
		150			121	276	190										
		190			141	368	230										
		240			166	414	280										
		290			191	506	330										
		340			216	598	380										
60	(40)	1~	D25FJ-60	120	106	230	160	77									
	150			121	276	190											
	190			141	368	230											
	240			166	414	280											
	290			191	506	330											
	340			216	598	380											