

★ 产品特点: 主体材质是聚缩醛树脂, 刚度高, 耐磨性好, 可用于食品行业。与标准型相比, 公差范围大, 如更需要高精度, 请选用标准型。

①代号	□材质	使用温度范围(°C)
OFEFZ	聚缩醛树脂含润滑剂与特殊填充剂	-40~80



①代号 - ②d - ③L
OFEFZ - d12 - L16

型号		③L										D	H	T	倒角b				
①代码	②d																		
OFEFZ	3	+0.054 +0.014	2.25	4.25									4.5	7.5	0.75	0.3			
	4		2.25	5.25									5.5	9.5					
	5	+0.068 +0.020	3	4									7	11					
	6		3	4	5	7	9						8	12					
	8	+0.083		4.5	5	6.5	8.5	9	11					10	15				
	10	+0.025		4	5	6	7	8	9	11	14	16			12	18			
	12			3	4	5	6	8	9	11	12	14	16	17	19	1	0.5		
	14			4.2	7	9	11	16						16	22				
	15	+0.102 +0.032				8	11	14	16	19	24			17	23				
	16							11	16						18	24			
	18								11	16	19					20	26		
	20								10	15	20					23	30		
	22	+0.124							10						25	33	1.5	0.8	
	25	+0.040							10	15	20					28			35
	30					7				14	24	30	35			34			42
35									14	24					39	47			
40	+0.150									28	38			44	52	2	1.2		
45	+0.050								23	43	48			50	58				
50									18	28	38	48			55			63	

▲ d公差为压入标准H7座孔(ISO3547-1)后公差。

5天发货

数量	1-9	10~
折扣率	100%	现询

B2 无油衬套