

# 干式衬套



★ 产品特点: 复合层型、肩型; 薄壁且紧凑的规格。

**最大降幅 30%**

①代号	类型	M材质			使用温度范围 (°C)
		基板	中间层	工作面	
OFFZB	直柱型	SPCC镀锡	球形青铜粉	改性聚四氟乙烯 (PTFE)	-195~280
OFFZF	肩型				
OFFZW	止推垫片				

OFFZB 直柱型      OFFZF 肩型      OFFZW 止推垫片

视角标准: 第一视角

①代号 - ②d - ③L

OFFZB - d20 - L30

订购编号示例

型号	③L			OFFZB			OFFZF			推荐轴径公差	基座孔推荐公差 (H7)	压入后内径公差			
	①代号	②d	③L	D	T	a	D	H	T/T1				T公差	a	
OFFZB 直柱型	3	3 4 5 (6)	5	+0.047 +0.017			4.6	7	0.8		-	-0.025 -0.034	+0.012 0	+0.062 0	
	4	3 4 5 6 (8)	6				5.6	9							
	5	3 4 5 6 8	7				7	10							
	6	3 4 5 6 8 10 12	8	+0.055 +0.025			8	12					-0.025 -0.037	+0.015 0	+0.065 0
	8	3 4 5 6 8 10 12 15	10				10	15					-0.025 -0.040		
	10	5 6 8 10 12 15 20	12				12	18		0					
	12	5 6 8 10 12 15 20	14	+0.060 +0.030	1.0	±0.025	0.3	14	20						
	13	5 6 8 10 12 15 20	15				15	21	1.0	-0.025		0.3		+0.018 0	+0.068 0
	15	5 6 8 10 12 15 20 25 30	17	+0.065 +0.035			17	23					-0.025 -0.043		
	16	8 10 12 15 20 25 30	18	+0.070 +0.035			18	24							
OFFZF 带肩型	18	8 10 12 15 20 25 30 35	20	+0.075 +0.040			20	26						+0.071 0	
	20	8 10 12 15 20 25 30 35	23	+0.080 +0.045			23	31						+0.021 0	+0.081 0
	22	8 10 12 15 20 25 30 35 40	25				25	33	1.5		0.5		-0.025 -0.046		
	25	10 12 15 20 25 30 35 40 (50)	28	+0.085 +0.050			28	36		0					
	30	10 12 15 20 25 30 35 40 50	34	+0.090 +0.050			34	42		-0.030				+0.025 0	+0.085 0
	35	10 12 15 20 25 30 35 40 50	39	+0.095	2.0		39	49	2.0						
	40	10 12 15 20 25 30 35 40 50 60	44	+0.055		0.8	44	54			0.8		-0.025 -0.050		
	50	12 15 20 25 30 35 40 50 60	55	+0.105 +0.060	2.5	±0.040	55	65	2.5	0 -0.040			+0.030 0	+0.110 0	

L(0)尺寸仅限OFFZB。轴径为推荐尺寸OFFZB/OFFZF皆为开口卷制衬套,上表中公差皆为压入环规(±0.002)后的参考值。

①代号	②规格	T	D	D <sub>1</sub>	安装孔			适用衬套内径
					P	容差	P.C.D	
OFFZW	6	1.5	8	16	1.0	+0.30 +0.10	12	6
	8		10	18			14	8
	10		12	24			18	10
	12		14	26			20	12
	14		16	30			23	13
	16		18	32	25	15-16		
	18		20	36	28	18		
	20		22	38	30	20		
	22		24	42	33	22		
	25		28	48	38	25		
	30		32	54	43	30		
	35		38	62	50	35		
	40		42	66	54	40		
	50		52	78	65	50		

交货期

**1**天发货

数量

1-9    10~

优惠价

折扣率

100%    现询

B2 无油衬套