



带挡边滚针轴承 标准型 开式 · 无密封带内圈

★ 产品特点：主要用于转速较低的机件上



①代号	类型			轴承材料	
	标准型	开式	无密封带内圈	国标	相当
BLF				GCr15	SUJ2



视角标准：第一视角





型号
BLF-NK15/12

订购编号示例

①代号	型号		d	F	D	B	r min	S	基本额定负载		疲劳极限载荷 Cur N	极限转速 rpm	参考转速 rpm	重量 (g)	
	②轴承型号								Cr(动) N	Cor(静) N					
BLF	NK15/12	-	5	8	15	12		1.5	4450	4100	690	32500	32500	11.5	
	NK15/16	-				16		2	5800	5800	970		32000	15.3	
	NK16/12	-	6	9	16	12		1.5	5100	5000	840	31000	28500	13.5	
	NK16/16	-				16		2	6600	7100	1190		28000	17.4	
	NK17/12	-	7	10	17	12		1.5	5300	5500	930	29500	26000	13.7	
	NK17/16	-				16		2	7000	7800	1310		25500	18.2	
	NK19/12	-	9	12	19	12		1.5	7200	7100	1280	26500	20200	16.6	
	NK19/16	-				16		2	10100	11000	1920		19500	21.9	
	NK110/16	-	10	14	22	16			11400	11500	2100	24600	16400	29.4	
	NK110/20	-				20		0.3	14500	15600	2700		16100	37.1	
	-	NA4900	-			13			9600	9200	1630	25000	17300	23	
	NK112/16	-	12	16	24	16			12800	13900	2550	23200	14500	33.3	
	NK112/20	-				20			16300	18800	3250		14200	41.9	
	-	NA4901	-			13			10600	10900	1940	23600	14900	26	
	-	NA6901	-			22		1	18100	21600	3800		13900	46	
	NK115/16	-	15	19	27	16			14700	17400	3200	21600	12400	38.8	
	NK115/20	-				20		0.5	18700	23600	4150		12100	48.7	
	-	NA4902	-			13			12000	13600	2430		12000	34	
	-	NA6902	-			23		1	19500	25500	4450		11700	63.6	
	-	-	NKIS15			22	35	20	0.6	27500	28000	4900	19600	10300	92
	NK117/16	-	17	21	29	16			15200	18700	3450		11400	42.4	
	NK117/20	-				20		0.3	19300	25500	4450	20600	11200	53.4	
	-	NA4903	-			13			12400	14600	2600		10900	37	
	-	NA6903	-			23		1	21100	29000	5100		10500	72	
-	-	NKIS17			37	20	0.6	29500	31000	5400	18100	9500	98		
NK120/16	-	20	24	32	16			16900	22300	4100	18500	10100	49		
NK120/20	-				20		0.3	21400	30500	5300		9900	61		
-	NA4904	-			17			23700	25500	4600	17200	9600	75.2		
-	NA6904	-			30		1	40500	51000	9100		9200	141		
-	-	NKIS20			28	42	20	0.6	32500	36500	6400	15800	8300	129	
NK122/16	-	22	26	34	16			17300	23600	4350	17200	9500	52		
NK122/20	-				20			22000	32000	5600		9300	65.4		
-	NA49/22	-			17			0.8	26000	29500	5300	16100	8700	80	
-	NA69/22	-			30		0.3	0.5	42000	55000	9900		8500	150	
NK125/20	-	25	29	38	20			1	27500	39000	6900	15300	8100	75.8	
NK125/30	-				30			1.5	37000	57000	10600		8200	124	
-	NA4905	-			17			0.8	26500	31500	5700	14600	7900	88	
-	NA6905	-			30			1	44000	59000	10600		7700	161	
-	-	NKIS25			47	22	0.6	1	38000	43500	7400	13600	7400	162	
NK128/20	-	28	32	42	20			0.5	29500	44500	7800	14000	7500	92.4	
NK128/30	-				30			1.5	39000	63000	11700		8600	146	
-	NA49/28	-			17			0.8	27500	33500	6100	13400	7200	97.7	
-	NA69/28	-			30		0.3	1	45500	63000	11400		7000	182	
NK130/20	-	30	35	45	20			0.5	31000	48500	8500	12900	6800	108	
NK130/30	-				30			1	46000	81000	15000		6600	165	
-	NA4906	-			17			0.8	28500	35500	6400	12700	6800	101	
-	NA6906	-			30			1	49000	71000	12900		6400	192	
-	-	NKIS30			52	22	0.6	1	41500	50000	8600	12000	6600	184	
NK132/20	-	32	37	47	20			0.5	28000	43500	7600	12300	6900	118	
NK132/30	-				30			1	42000	73000	13500		6600	180	
-	NA49/32	-			40	52	20	0.6	0.8	34500	47500	8900	11700	6500	158
NK135/20	-	35	40	50	20			0.5	33500	56000	9800	11400	6100	122	
NK135/30	-				30			1	44000	79000	14600		6200	193	
-	NA4907	-			42	55	20	0.6	0.8	35500	50000	9400	10900	6000	170
-	-	NKIS35			58	22		0.5	44000	57000	9800	10500	5900	220	
NK138/20	-	38	43	53	20			1	30500	51000	8900		6000	136	
NK138/30	-				30			0.5	45500	85000	15800	10700	5900	207	
NK140/20	-	40	45	55	20			1	35000	62000	10800	10200	5600	136	
NK140/30	-				30			0.5	52000	103000	19100		5400	216	
-	NA4908	-			48	62	22	0.6	1	48500	67000	11500	9600	5300	230
-	-	NKIS40			50	65	22	1	0.5	48000	67000	11500	9300	5200	281
NK142/20	-	42	47	57	20			1	32500	56000	9900		5600	148	
NK142/30	-				30			0.3	1	48500	94000	17500	9800	5400	222
NK145/25	-	45	50	62	25			1.5	48500	87000	14800	9200	5300	217	
NK145/35	-				35			2	67000	132000	23900		4950	308	
-	NA4909	-			52	68	22	1	1	51000	73000	12600	8700	4750	271
-	-	NKIS45			72	22	1	0.5	51000	74000	12700			336	
NK150/25	-	50	55	68	25			1.5	45500	82000	14000	8400	4950	270	
NK150/35	-				35			2	60000	118000	21300		4900	379	
-	NA4910	-			58	72	22	1	1	53000	80000	13800	8000	4350	274
-	-	NKIS50			60	80	28	1.1	2	71000	98000	17300	7500	4450	518

- ▲ 1kgf=9.8N
- ▲ 不承诺此产品品牌
- ▲ 更多规格请咨询客服



交货期

4天发货