



## Electronic thermostat / hygrostat, ETF300

- Description:** Electronic hygrostat-thermostat monitors the relative humidity and the temperature independently of each other, and it manages heaters and filter fans to prevent condensation and corrosion inside the enclosure. Mounting clip for 35 mm DIN rail (EN 60715).
- Setting range:** 0°C to 60°C, and 40 to 90% R.H.
- Material:** Plastic according to UL94 V-0.
- Switch capacity:** 240V AC, 8(3)A. 120V AC, 8(3)A. 24V DC, 4A. Value in brackets for inductive load.
- Operating temperature:** -20°C to +60°C.
- Service life:** 50,000 cycles.
- Connection:** Pole terminal for 2.5 mm<sup>2</sup>.
- Protection:** IP 20.
- Approvals:** CE, EAC, cULus\_UL Listed.
- Finish:** RAL 7035.
- Pack quantity:** 1 piece.



Voltage (V)	Frequency	Item no.
230V AC	50/60 (Hz)	ETF300
115V AC	50/60 (Hz)	ETF300120



Electric diagram

