



Korpus formy

Mold base

218x296




Wymiary i tolerancje
Dimensions and tolerances



	A	B	C
PK	244	186	172


PK 01



PK 01 – 218 x 296 x h / material

27	1730
36	2312
	2085



PK 11



PK 11 – 218 x 296 x h / material

27	1730
36	2312
	2085



PK 02



PK 02 – 218 x 296 x h / material

22	1730
27	2312
36	2085


PK 12



PK 12 – 218 x 296 x h / material

22	1730
27	2312
36	2085



PK 21



PK 21 – 218 x 296 x h / material

22	1730
27	2312
	2085

PK 22




PK 22 – 218 x 296 x h / material

17	1730
22	2312
27	2085

**PK 03
PKA 03**

Podcięcia do demontażu
na życzenie.
Corner undercuts upon request.




PK 03 – 218 x 296 x h / material

PK 35 – 218 x 296 x h / material (a1/b1/h1)

17	1730
22	2083
27	2085
36	2162
46	2311
56	2312
66	2738
76	Toolox33
86	Toolox44
96	2738HH
	2714HH

**PK 35
PKA 35**

Podcięcia do demontażu
na życzenie.
Corner undercuts upon request.



Material info





Korpus formy

Mold base

218x296

PK 31



Podcięcia do demontażu na życzenie.
Corner undercuts upon request.





Material info



PK 31 – 218 x 296 x h / material

h	material
17	1730
22	2083
27	2085
36	2162
46	2311
56	2312
66	2343
76	2738
86	2767
96	Toolox33
	Toolox44
	2738HH
	2714HH



PK 04



PK 04 – 218 x 296 x h / material

h	material
27	1730
36	2312
46	2085
56	



PK 05



PK 05 – 218 x 296 x h / material

h	material
56	1730
76	2085
96	


PK 55




PK 55 – 218 x 296 x h / material

h	material
56	1730
76	2085
96	

PK 06



	A	B
PK 06	230	108




PK 06 – 218 x 296 x h / material

h	material
12	1730
	2085

PK 65



	A	B
PK 65	230	76




PK 65 – 218 x 296 x h / material

h	material
12	1730
	2085

PK 07




	A	B	D
PK 07	230	108	266




PK 07 – 218 x 296 x h / material

h	material
17	1730
	2312
	2085

PK 75



	A	B	D
PKA 75	230	76	266



PK 75 – 218 x 296 x h / material

h	material
17	1730
	2312
	2085