





# SÄULENGESTELL



201.33.



## Führungsart



Bestell-Nr. Teil 2  
Ohne Zapfengewinde  
im Oberteil



## 201.33. Säulengestell

Bestell-Nummer Teil 1*	Arbeitsfläche													
	a <sub>1</sub> x b <sub>1</sub>	a <sub>2</sub>	b <sub>2</sub>	C <sub>1</sub>	C <sub>2</sub>	C <sub>3</sub>	C <sub>4</sub>	d <sub>2</sub>	e	e <sub>3</sub>	e <sub>4</sub>	f	l	r
201.33.063.050.□□□.□□	63 x 50	116	110	25	25	40	45	16	72	88	74	57	125 - 355	22
201.33.080.060.□□□.□□	80 x 60	116	117	25	25	40	45	20	72	95	81	62	160 - 400	22

\*Bestell-Nummer Teil 2 = Führungsart und Führungssäulen-Typ/-Länge ergänzen  
 Bestell-Beispiel siehe Anfang des Kapitels A Guss-Säulengestelle