


冲头, 毛坯, DIN 9861, D 型

2209.




2209. 冲头, 毛坯, DIN 9861, D 型

d ₁ / 订购数字	d ₂	k	l (订货字母)	71 (D)	80 (E)	100 (G)	120 (J)
3/(1)	4.5	0.5		●	●	●	●
4/(2)	5.5	0.5		●	●	●	●
5/(3)	6.5	0.5		●	●	●	●
6/(4)	8	0.5		●	●	●	●
8/(5)	10	1		●	●	●	●
10/(6)	12	1		●	●	●	●
13/(7)	15	1		●	●	●	●
16/(8)	18	1.5		●	●	●	●
20/(9)	22	1.5		●	●	●	●

订购示例:

2 2 0 9 . 3 7 G



长度: l
100 mm
直径: d₁
13 mm
材料:
HSS
型号:
DIN 9861
规格:
毛坯
冲头:
无弹顶销

订货字母
= (G)
订购数字
= (7)
订购数字
= (3)
订购数字
= (9)
订购数字
= (0)
= 22

材料:

HSS
订货号 2209.3.
ASP 2023
订货号 2209.6.

硬度:

杆部 64 ± 2 HRC
头部 52 ± 5 HRC

☞ 材料说明和其他材料见E章开头。

结构:

在凸模头部热墩和回火处理后, 用切入磨削法精磨凸模柄部。

根据要求可提供其他直径和长度!