

PRECISION FLAT AND SQUARE BAR STEEL WITH MACHINING ALLOWANCE, DIN 59350

Material:

1.2379 / X 155 CrVMo 12-1
Cold worked steel

2923.2379.




Execution:

Thickness precision ground, width ground or milled, length machined

Note:

- = available in 500 mm and 1000 mm lengths
- = only available in 500 mm lengths
- = only available in 1000 mm lengths



2923.2379. Precision flat and square bar steel with machining allowance, DIN 59350

s	2.2	3.2	4.2	5.2	6.2	8.2	10.4	12.4	15.4	16.4	20.4	25.4	30.4	32.4	40.4	50.4	60.4	63.4	70.4	80.4	100.4	120.4	150.4	
b																								
6.2						○																		
8.2						●																		
10.3	●	●	●	●	●	●																		
10.4							●																	
12.4								●																
15.3	●	●	●	●	●	●	●	●	■															
15.4									●															
16.4										■														
20.3	●	●	●	●	●	●	●	●	●	■														
20.4											●													
25.3	●	●	●	●	●	●	●	●	●	■	●													
25.4												●												
30.3	●	●	●	●	●	●	●	●	●	■	●	●												
30.4													●											
32.3							■	■	■		■	■												
32.4																						■		
40.3	●	●	●	●	●	●	●	●	●	■	●	●	●											
40.4																								
50.3	●	●	●	●	●	●	●	●	●	■	●	●	●	■										
50.4																								
60.3	●	●	●	●	●	●	●	●	●		●	●	●											
60.4																								
63.3							■	■	■		■	■												
63.4																								
70.3	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
70.4																								
80.3	●	●	●	●	●	●	●	●	●	■	●	●	●	■										
80.4																								
90.3							■	■	■		■	■	■	■	■	■	■	■	■	■	■	■	■	■
100.3	●	●	●	●	●	●	●	●	●	■	●	●	●	■	●	●	●	■	■	■	■	■	■	■
100.4																								
120.4																								
125.3	●	●	●	●	●	●	●	●	●	■	●	●	●	■	●	●	■	■	■	■	■	■	■	■
150.3	●	●	●	●	●	●	●	●	●	■	●	●	●	■	●	●	■	■	■	■	■	■	■	■
150.4																								
160.3							■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
200.3	●	●	●	●	●	●	●	●	●	■	●	●	●	■	●	●	■	■	■	■	■	■	■	■
250.3	●	●	●	●	●	●	●	●	●	■	●	●	●	■	●	●	■	■	■	■	■	■	■	■
300.3	●	●	●	●	●	●	●	●	●	■	●	●	●	■	●	●	■	■	■	■	■	■	■	■
350.3										■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
400.3										■	■	■	■	■	■	■	■	■	■	■	■	■	■	■

Ordering Code (example):

Precision flat and square bar steel with machining allowance, DIN 59350	=	2923.2379.
Width B	15.3 mm =	015.
Thickness S	2.2 mm =	002.
Length L	500 mm =	0500
Order No	=	2923.2379. 015.002.0500