


带有圆锥形头部的导正销, ISO 8020

2261.




2261. 带有圆锥形头部的导正销, ISO 8020

| d ₁ / 订购数字 | d ₂ | T | P | l ₁ / 订购数字 | N | l / (订货字母) | 63 (C) | 71 (D) | 80 (E) | 90 (F) | 100 (G) | 110 (H) | 125 (K) | 140 (L) |
|-----------------------|----------------|---|-------------|-----------------------|----|------------|-----------|-----------|-----------|-----------|------------|------------|------------|------------|
| 5 / (3) | 8 | 5 | 1 - 4,9 | 13 (3) | 4 | | ● | ● | | | | | | |
| 6 / (4) | 9 | 5 | 1,6 - 5,9 | 13 (3) | 5 | | ● | ● | ● | | | | | |
| 8 / (5) | 11 | 5 | 2,5 - 7,9 | 13 (3) | 6 | | ● | ● | ● | ● | | | | |
| 10 / (6) | 13 | 5 | 4 - 9,9 | 13 (3) 19 (4) | 8 | | ● | ● | ● | ● | ● | | | |
| 13 / (7) | 16 | 5 | 5 - 12,9 | 13 (3) 19 (4) | 10 | | ● | ● | ● | ● | ● | ● | | |
| 16 / (8) | 19 | 5 | 8 - 15,9 | 13 (3) 19 (4) 25 (5) | 15 | | ● | ● | ● | ● | ● | ● | ● | |
| 20 / (9) | 23 | 5 | 12 - 19,9 | 13 (3) 19 (4) 25 (5) | 20 | | ● | ● | ● | ● | ● | ● | ● | ● |
| 25 / (10) | 28 | 5 | 16,5 - 24,9 | 13 (3) 19 (4) 25 (5) | 25 | | ● | ● | ● | ● | ● | ● | ● | ● |
| 32 / (11) | 35 | 5 | 20 - 31,9 | 19 (4) 25 (5) | 30 | | ● | ● | ● | ● | ● | ● | ● | ● |

订购示例:

2 2 6 1 . 6 G 3 . 0 7 1 0



形状: 圆形
 P = ∅ 7,1 mm
 冲裁凸模长度: l₁
 13 mm
 长度: l
 100 mm
 直径: d₁
 10 mm
 型号:
 ISO
 规格:
 圆锥尖部导正销
 冲头:
 无弹顶销

= 0710
 订购数字
 = (3)
 订货字母
 = (G)
 订购数字
 = (6)
 订购数字
 = (1)
 订购数字
 = (6)
 = 22

材料:

HSS

硬度:

杆部 64 ± 2 HRC

头部 52 ± 5 HRC

结构:

头部热镀。肩部, 轴部及前端精磨加工。

特别生产请洽询。