


PIASTRA DI SCORRIMENTO, ACCIAIO, CNOMO




2962.84.45.




A



B



2962.84.45.



Materiale:

Acciaio, temprato in superficie

Nota:

La fornitura non comprende le viti.

Fissaggio:

Utilizzare viti con testa cilindrica
DIN EN ISO 4762 M10.

2962.84.45. Piastra di scorrimento, Acciaio, CNOMO

N. d'ordine	Forma	b	a	l_1	Numero fori per viti	Numero filettature
2962.84.45.050.17.160	A	50	160	38	2	2
2962.84.45.050.17.250	B	50	250	38	3	3
2962.84.45.080.17.160	A	80	160	68	2	2
2962.84.45.080.17.250	B	80	250	68	3	3