


带喇叭颈的冲头，毛坯，带弹顶销，DIN 5118 E 型

2706.




2706. 带喇叭颈的冲头，毛坯，带弹顶销，DIN 5118 E 型

d ₁ / 订购数字	d ₂	a	k	r	l (订货字母)	71 (D)	80 (E)	90 (F)	100 (G)	120 (J)
5 / (3)	7	1.5	4	10		●	●	●	●	●
6 / (4)	9	1.5	4	10		●	●	●	●	●
8 / (5)	11	1.5	4	12		●	●	●	●	●
10 / (6)	14	1.5	4	15		●	●	●	●	●
13 / (7)	17	1.5	4	15		●	●	●	●	●
16 / (8)	20	1.5	4	15		●	●	●	●	●
20 / (9)	25	1.5	4	15		●	●	●	●	●

订购示例:

2706.7G



长度: l
100 mm
直径: d₁
13 mm
型号:
带锥形头
规格:
毛坯
冲头:

订货字母
= (G)
订购数字
= (7)
订购数字
= (6)
订购数字
= (0)
有压紧销
= 27

材料:

HSS

硬度:

杆部 62-66 HRC

头部 45-55 HRC

材料说明和其他材料见E章开头。

结构:

凸模杆部已精磨。凸模头部已热锻并退火。

说明:

匹配的先导式总钻 2284.00.