


For new constructions:  
**Series 15 "Zipper"**  
▶ page 4.16

# Series 15 classic Zipper



igus® E-ChainSystems®





- ① "Zipper-fast" opening & closing
- ② Proven for high acceleration
- ③ Zipper lids can be separated and joined at each chain link
- ④ Very small pitch for optimum low noise, smooth motion
- ⑤ Mounting brackets with integrated strain relief
- ⑥ Interior separation with Vertical separators possible
- iF-Design-Award Winner






Phone +49- (0) 22 03-96 49-800  
Fax +49- (0) 22 03-96 49-222

igus® GmbH  
51147 Cologne



**Unsupported length**

FL<sub>G</sub> = with straight upper run  
FL<sub>B</sub> = with permitted sag




**Series 15 classic - zip-open along the outer radius**

Part No.	Bi [mm]	Ba [mm]	R [mm] Bending Radii
15.1.□.0	15	26	038 048 075
15.2.□.0	25	36	110 125 145
15.3.□.0	38	49	180
15.4.□.0	50	61	180
			Radii for all widths!

Supplement Part No. with required radius. Example: 15.1.100.0  
Bending radii listed above can be combined with every chain width!

**Part No. structure**



- Order example 2,0 m complete E-Chain®**  
(indicate chain-lengths or number of links)
- 2,0 m (66 links) **Series 15.1.100.0**
  - + 2 separators **152** assembled each 2<sup>nd</sup> link
  - + 1 set mounting brackets + **tiewrap plates 101.12PZ**