



PLAQUE DE FROTTEMENT, BRONZE AVEC LUBRIFIANT SOLIDE, VDI 3357

2960.77.



2960.77.



2960.77. Plaque de frottement, Bronze avec lubrifiant solide, VDI 3357

N° de commande	Forme	b	l ₁	l ₂	l ₃	l ₄	l ₅	d	d ₁	t	Nombre de perçages
2960.77.080.200	A	80	200	25	175	0	0	13.5	20	13	2
2960.77.080.250	B	80	250	25	85	165	225	13.5	20	13	4
2960.77.080.300	B	80	300	25	105	195	275	13.5	20	13	4
2960.77.080.350	B	80	350	25	125	225	325	13.5	20	13	4
2960.77.080.400	B	80	400	25	145	255	375	13.5	20	13	4
2960.77.080.450	B	80	450	25	165	285	425	13.5	20	13	4
2960.77.080.500	B	80	500	25	175	325	475	13.5	20	13	4

Matière :

Bronze avec lubrifiant solide

Remarque :

Livraison sans les vis.

Fixation :

Utiliser des vis à tête cylindrique
DIN EN ISO 4762 M12.