


Part No. structure



Series R68 - snap-open along outer radius

Part No.	B_i [mm]	B_a [mm]	R [mm]	Bending radii								Weight [kg/m]
68.050.	50	68	100	125	150	175	200	225	250	300	≈ 1,90	
68.075.	75	93	100	125	150	175	200	225	250	300	≈ 2,18	
68.100.	100	118	100	125	150	175	200	225	250	300	≈ 2,46	
68.115.	115	133	100	125	150	175	200	225	250	300	≈ 2,63	
68.125.	125	143	100	125	150	175	200	225	250	300	≈ 2,77	
68.150.	150	168	100	125	150	175	200	225	250	300	≈ 3,05	
68.175.	175	193	100	125	150	175	200	225	250	300	≈ 3,36	
68.200.	200	218	100	125	150	175	200	225	250	300	≈ 3,64	
68.225.	225	243	100	125	150	175	200	225	250	300	≈ 3,92	
68.250.	250	268	100	125	150	175	200	225	250	300	≈ 4,23	

 Supplement Part No. with required radius. Example: 68.100. 100.0

0 = standard color, other colors ► page 1.39 · Pitch = 36 mm/link - Links/m = 28



Hot Chips up to 850°C

E-Tubes that repel hot chips, up to 850 °C. Some applications, depending on amount and size of the chips, can burn or melt the surface. That is no longer the case with the igus® "igumid HT" material.

Order example - Full E-Tube made of HT*: **68.100.100.0.HT**

Order example - Lids made of HT: **68.100HT.100.0**

*for long travels upon request

Delivery time up to 4 weeks! Further Information: www.igus.de/en/HT

