




## Version ZF14 | "easy" design, split crossbar along the inner radius


Part No.	<i>Bi</i>	<i>Ba</i>	<i>R</i> Available bend radii	Weight
e-chains®	[mm]	[mm]	[mm]	[kg/m]
ZF14.038.R.0	38	46.6	028	≈ 0.297

Complete Part No. with required radius (*R*). Example: ZF14.038.028.0

## Installation dimensions



Inner height [mm]	21
Pitch [mm/link]	30.5
Links/m	33
corresponds to [mm]	1,006.5
Chain length	$L_K = S/2 + K$



<i>R</i>	028
<i>H</i> <sup>+5</sup>	86
<i>D</i>	116,5
<i>K</i>	211

The required clearance height:  $H_F = H + 10$  mm (with 0.2 kg/m fill weight)