



PLETINA DE GUÍA, BRONCE CON LUBRIFICANTE SOLIDO, VDI 3387

2960.89.



2960.89.



2960.89. Pletina de guía, Bronce con lubricante solido, VDI 3387

Código	Forma	b	a	l ₁	l ₂	e	e ₁	d	d ₁	f	c	t	r	Número de orificios
2960.89.063.180	A	63	180	20	90	50	36	14	20	18	36	16	16	3
2960.89.063.200	A	63	200	20	90	50	36	14	20	18	36	16	16	3
2960.89.063.224	A	63	224	20	90	50	36	14	20	18	36	16	16	3
2960.89.071.180	A	71	180	20	90	50	36	14	20	18	36	16	16	3
2960.89.071.200	A	71	200	20	90	50	36	14	20	18	36	16	16	3
2960.89.071.224	A	71	224	20	90	50	36	14	20	18	36	16	16	3
2960.89.090.200	A	90	200	20	100	50	50	18	26	28	45	21	25	3
2960.89.090.224	A	90	224	20	100	50	50	18	26	28	45	21	25	3
2960.89.090.250	A	90	250	20	100	50	50	18	26	28	45	21	25	3
2960.89.112.200	A	112	200	20	100	50	50	18	26	28	45	21	25	3
2960.89.112.224	A	112	224	20	100	50	50	18	26	28	45	21	25	3
2960.89.112.250	A	112	250	20	100	50	50	18	26	28	45	21	25	3
2960.89.140.315	B	140	315	40	150	80	90	22	33	36	45	25,5	31,5	4
2960.89.190.400	B	190	400	40	150	80	90	22	33	36	56	25,5	31,5	4
2960.89.240.500	B	240	500	40	250	160	160	26	40	36	56	30,5	31,5	4
2960.89.240.630	B	240	630	40	250	160	160	26	40	36	56	30,5	31,5	4

Material:

Bronce con lubricante sólido, de bajo mantenimiento

Nota:

Se suministro sin los tornillos.

Sujeción:

Emplear tornillos Allen cilíndricos DIN EN ISO 4762.