




### The Standard - Option KMA\* - pivoting

- Recommended for unsupported and gliding applications
- Confined installation conditions
- Option - integrated C-profile strain relief device with Chainfix clip or strain relief tiwrap plates
- Corrosion resistant
- Universal mountable with attachment capability on all sides

\*KMA = Polymer Metal Mounting Bracket



The attachment variants arising automatically by the choice of the KMA mounting bracket




### Option KMA - locking


- Recommended for vertical hanging / standing applications

#### Additionally:

- Universal mountable
- C-profile option
- Corrosion resistant
- Locked connections
- At very high acceleration




The attachment variants arising automatically by the choice of the KMA mounting bracket



Moving end 141400/189400...2 (pivoting)  
140400/188400...2 (locking)

Fixed end (pivoting) 141400/189400...1  
(locking) 140400/188400...1



### Dimensions and order configurations

#### Part No. structure (pivoting)

141400. 189400.	07.	12.	C
			Optional with C-profile
			Full set
			Width
			141400 = E-Chain*
			188400 = E-Tube

#### Part No. structure (locking)

140400. 188400.	07.	12.	C
			Optional with C-profile
			Full set
			Width
			140400 = E-Chain*
			188400 = E-Tube

Width index	Part No. full set pivoting	Part No. full set locking	C-profile option [mm]	Width index	Part No. full set pivoting	Part No. full set locking	C-profile option [mm]
.05.	▶ 141400	140400	.05.12. C 50	.31.	▶ 141400	140400	.31.12. C 312
.06.	▶ 141400	140400	.06.12. C 65	.32.	▶ 141400	140400	.32.12. C 325
.07.	▶ 141400/189400	140400/188400	.07.12. C 75	.33.	▶ 141400	140400	.33.12. C 337
.08.	▶ 141400	140400	.08.12. C 87	.35.	▶ 141400/189400	140400/188400	.35.12. C 350
.10.	▶ 141400/189400	140400/188400	.10.12. C 100	.36.	▶ 141400	140400	.36.12. C 362
.11.	▶ 141400	140400	.11.12. C 112	.37.	▶ 141400	140400	.37.12. C 375
.12.	▶ 141400/189400	140400/188400	.12.12. C 125	.38.	▶ 141400	140400	.38.12. C 387
.13.	▶ 141400	140400	.13.12. C 137	.40.	▶ 141400/189400	140400/188400	.40.12. C 400
.15.	▶ 141400/189400	140400/188400	.15.12. C 150	.41.	▶ 141400	140400	.41.12. C 412
.16.	▶ 141400	140400	.16.12. C 162	.42.	▶ 141400	140400	.42.12. C 425
.17.	▶ 141400/189400	140400/188400	.17.12. C 175	.43.	▶ 141400	140400	.43.12. C 437
.18.	▶ 141400	140400	.18.12. C 187	.45.	▶ 141400	140400	.45.12. C 450
.20.	▶ 141400/189400	140400/188400	.20.12. C 200	.46.	▶ 141400/189400	140400/188400	.46.12. C 462
.21.	▶ 141400	140400	.21.12. C 212	.47.	▶ 141400	140400	.47.12. C 475
.22.	▶ 141400	140400	.22.12. C 225	.48.	▶ 141400	140400	.48.12. C 487
.23.	▶ 141400	140400	.23.12. C 237	.50.	▶ 141400	140400	.50.12. C 500
.25.	▶ 141400/189400	140400/188400	.25.12. C 250	.51.	▶ 141400	140400	.51.12. C 512
.26.	▶ 141400	140400	.26.12. C 262	.52.	▶ 141400	140400	.52.12. C 525
.27.	▶ 141400/189400	140400/188400	.27.12. C 275	.53.	▶ 141400	140400	.53.12. C 537
.28.	▶ 141400	140400	.28.12. C 287	.55.	▶ 141400	140400	.55.12. C 550
.30.	▶ 141400/189400	140400/188400	.30.12. C 300	.60.	▶ 141400	140400	.60.12. C 600

Full set, for both ends:

141400. 05. 12

Single-part order:

141400. 05. 2

Mounting bracket moving end

141400. 05. 1

Mounting bracket fixed end