

# 482.6 mm (19") installation system

## Mounting angles

### Mounting angles, 482.6 mm (19")

for TS

#### L-shaped

The L-shaped mounting angles accommodate the installation kits of server systems. The integral U markings in the front facilitate systematic assembly within the 482.6 mm (19") attachment level.

#### Technical specifications:

- 2 mm sheet steel
- Integral 482.6 mm (19") punchings (EIA standard)
- Side round and square punchings
- Clear chromated for conductive connection of the 482.6 mm (19") installed equipment

#### Supply includes:

- Assembly parts

Full installation Rack height mm	U	Packs of	Model No.
1800	38	2 pc(s).	<b>7827.181</b>
2000	42	2 pc(s).	<b>7827.201</b>
2200	47	2 pc(s).	<b>7827.221</b>



#### Also required:

- TS punched sections with mounting flanges or TS installation brackets as installation kit for mounting angles, see page 685
- Attachment of component shelves: Adaptor 7827.300, see page 632

#### Technical details:

Available on the Internet



### Installation bracket TS

for L-shaped mounting angles in TS, 482.6 mm (19")

For upgrading existing DK-TS applications.

#### Installation in enclosure width 800 mm

The installation brackets are screw-fastened to the enclosure frame in the enclosure width. The mounting angle is attached to the depth stay at the top and bottom. The brackets ensure optimum clearance at the sides for cable routing. For partial enclosure configuration, the installation brackets may be attached to the TS punched sections with mounting flanges 17 x 73 mm, on the outer attachment level of the enclosure frame. Fully depth-variable attachment is facilitated by the attachment slots.

Installation position	Packs of	Model No.
Centre	2 pc(s).	<b>7827.480</b>

#### Material:

- Sheet steel

#### Surface finish:

- Zinc-plated


#### Supply includes:

- Assembly parts



#### Accessories:

- For partial installation, TS punched section with mounting flange, 17 x 73 mm, see page 606 – 607
- For partial installation, mounting angles, L-shaped, see page 685



### TS punched section with mounting flange as installation kit

for L-shaped mounting angles, 482.6 mm (19") in TS 482.6 mm (19")

For upgrading existing DK-TS applications.

#### Installation in enclosure width 600 mm

The installation kit consists of 4 TS punched sections with mounting flange 17 x 73 mm to accommodate mounting angles. One pack is sufficient for installing one or two 482.6 mm (19") mounting levels. For exceptionally heavy installed equipment, we recommend the installation of additional punched sections in the centre.

For enclosures		Packs of	Model No.
Width mm	Depth mm		
600	600	4 pc(s).	<b>8612.060</b>
600	800	4 pc(s).	<b>8612.080</b>
600	1000	4 pc(s).	<b>8612.000</b>
600	1200	4 pc(s).	<b>8612.020</b>

#### Material:

- Sheet steel

#### Surface finish:

- Zinc-plated

#### Supply includes:

- Assembly parts

