



**System accessories** Page 507 **Support arm systems** Page 135 **Stand systems** Page 164

For small operating units built into front panels. The front panel is inserted from the rear and secured with screw clamps. Special front panels with a material thickness of between 2 and 6 mm are possible. Rear panel optionally hinged on the left or right. Roof tray with cut-out and reinforcement for support arm system CP 40, steel.

**Design:**

- With support arm connection CP 40, steel

**Material:**

- Roof tray, base tray, rear panel: Aluminium
- Side parts: Extruded aluminium section
- Screw cover: Plastic

**Surface finish:**

- Roof tray, base tray, side parts: Powder-coated
- Rear panel: natural anodised

**Colour:**

- RAL 7024

**Protection category IP to**

- IEC 60 529:**
- IP 65

**Supply includes:**

- Roof tray
- Base tray
- Rear panel
- Side parts
- Screw cover
- Seal and screw clamp

**Technical details:**

Available on the Internet

Width mm	Packs of	241	241	315	315	Page
Height mm		238	388	238	388	
Depth mm		87	87	87	87	
To fit front panel width mm		178	178	252	252	
To fit front panel height mm		200	350	200	350	
<b>Model No.</b>	1 pc(s).	<b>6340.000</b>	<b>6340.100</b>	<b>6340.300</b>	<b>6340.400</b>	
Weight kg		2.8	3.8	3.4	4.5	

<b>Accessories</b>						
Front panels	1 pc(s).	6028.500	6028.510	6028.530	6028.540	704
Wall mounting bracket	1 set(s)	6341.000	6341.000	6341.000	6341.000	590
Spring nut M5	50 pc(s).	6108.000	6108.000	6108.000	6108.000	625
Cover plate	1 set(s)	6505.200	6505.200	6505.200	6505.200	704