

482.6 mm (19") installation system

482.6 mm (19") installation

Server telescopic slides

Facilitate optimum accessibility to the units, even when built-in.
For up to a maximum enclosure width of 426 mm.

Load capacity:

- 30 kg

Material:

- Sheet steel

Supply includes:

- 1 set =
 - 2 telescopic slides
 - Installation kit
 - Assembly parts

| For enclosure depth mm | Maximum extension mm | Model No. |
|------------------------|----------------------|-----------------|
| 600 | 511.2 | 3659.180 |
| 800 | 596.4 | 3659.190 |

Note:

- May only be fitted in conjunction with L-shaped 482.6 mm (19") sections



Mounting kit, 2 U

for 482.6 mm (19") equipment

Facilitates fast, simple integration of additional 2 U mounting space within an enclosure by attaching to the enclosure frame or to the existing mounting angles at the sides. The flexible slot fastening of the brackets means that the distance between the two installation brackets may be freely selected, so that other 482.6 mm (19") attachment dimensions may be implemented. The second row of holes is used for the optional configuration of additional mounting surfaces.

Material:

- Sheet steel

Surface finish:

- Zinc-plated

Supply includes:

- Assembly parts

| Packs of | Model No. |
|----------|-----------------|
| 2 pc(s). | 7246.420 |

