

Busbars E-Cu

To DIN EN 13 601.
Length: 2400 mm/bar.

Technical information:
Available on the Internet.

Dimensions mm	Approvals	Packs of	Model No. SV	Page
E-Cu				
12 x 5	UL	6	3580.000	
15 x 5	UL	6	3581.000	
20 x 5	UL	6	3582.000	
25 x 5	UL	6	3583.000	
30 x 5	UL	6	3584.000	
12 x 10	UL	6	3580.100	
15 x 10	UL	6	3581.100	
20 x 10	UL	6	3585.000	
30 x 10	UL	6	3586.000	
40 x 10	–	3	3587.000	
50 x 10	–	3	3588.000	
60 x 10	–	3	3589.000	
80 x 10	–	3	3590.000	
100 x 10	–	3	3590.010	
E-Cu tin-plated¹⁾				
30 x 5	–	6	3584.200	
30 x 10	–	6	3586.200	
Accessories				
Busbar connectors for busbars mm	12 x 5 – 15 x 10 (single connection)	3	9350.075	313
	20 x 5 – 30 x 10 (single connection)	3	9320.020	313
	20 x 5 – 30 x 10 (bayed connection)	3	9320.030	313
Busbar cover section for busbars mm	12/15 x 5	4	9350.010	311
	12/15 x 10	4	9350.060	311
	12 x 5 – 30 x 10	10	3092.000	311
	40 – 60 x 10	10	3085.000	311

¹⁾ Extended delivery times.

Busbar cover sections

Contact hazard protection via covering of the busbars. May be cut to required length.
Length: 1000 mm/section.

Material:

- Thermally modified hard PVC.
- Fire protection corresponding to UL 94-V0

Colour:

RAL 7035

Note:

Contact hazard protection, for more solutions see page 315.

Detailed drawings:

Available on the Internet.

For busbars mm	Approvals	Packs of	Model No. SV
12/15 x 5	–	4	9350.010
12/15 x 10	–	4	9350.060
12 x 5 – 30 x 10	UL	10	3092.000
40 – 60 x 10	–	10	3085.000

Inserted screw nuts M12

Self-holding nuts with knurled ring for busbars E-Cu.

Hole diameter: 14.5 mm.

Packs of	Model No. SV
30	3591.060

