

## Base/plinth TS



### Base/plinth, stationary for PC-TS, IW

Design-coordinated with the enclosures, height 100 mm, with front projection.

**Material:**  
Sheet steel, 2.0 mm

**Colour:**  
RAL 7035  
Design component, front: RAL 7015


**Supply includes:**  
1 design component, front  
1 base/plinth component, rear  
2 base/plinth trim panels, side

For depth mm	Model No. PC
600	<b>8800.920</b>

### + Accessories:

Attachment opportunities for:

- Twin castors PC 4634.500, see page 907,
- Levelling feet PS 4612.000, see page 906,
- Fastening bolts for cable clamp rails SO 2819.000, see page 896,
- Support bracket PS 4183.000, see page 1007.



### Filter mat

for

- Base/plinth component, vented
- Base/plinth component, vented, with designer trim panel

To cover the trim panel in the base/plinth component.

The mounting frame slides into position behind the filter mat in the base/plinth trim panel.

Filter class G3 to DIN EN 779.

**Supply includes:**  
Mounting frame.

For enclosure width mm	Packs of	Model No. DK
600	1	<b>7561.500</b>
800	1	<b>7581.500</b>

### Spare filter mat

**Supply includes:**  
Filter mat without mounting frame for base/plinth trim panels up to 800 mm wide.

	Packs of	Model No. DK
Spare filter mats	5	<b>7582.500</b>