


### Zylinderkopfschrauben

### Cylinder head cap screws

### Vis 6 pans creux

2



**SN3500-**

DIN EN ISO 4762-10.9

 SN3500-d-L



d	L	b	D1	K	d	L	b	D1	K
M3	8	6,5	5,5	3	M6	45	24,0	10,0	6
	12	10,5	5,5	3		50	24,0	10,0	6
	16	14,5	5,5	3		55	24,0	10,0	6
	20	18,0	5,5	3		60	24,0	10,0	6
	25	18,0	5,5	3		65	24,0	10,0	6
	30	18,0	5,5	3		70	24,0	10,0	6
M4	8	5,9	7,0	4	80	24,0	10,0	6	
	10	7,9	7,0	4	90	24,0	10,0	6	
	12	9,9	7,0	4	100	24,0	10,0	6	
	16	13,9	7,0	4	110	24,0	10,0	6	
	18	15,9	7,0	4	120	24,0	10,0	6	
	20	17,9	7,0	4	140	24,0	10,0	6	
	25	22,9	7,0	4	M8	12	8,3	13,0	8
	30	20,0	7,0	4		16	12,3	13,0	8
	35	20,0	7,0	4		18	14,3	13,0	8
	40	20,0	7,0	4		20	16,3	13,0	8
M5	10	7,6	8,5	5		25	21,3	13,0	8
	12	9,6	8,5	5		30	26,3	13,0	8
	16	13,6	8,5	5		35	31,3	13,0	8
	18	15,6	8,5	5		40	28,0	13,0	8
	20	17,6	8,5	5		45	28,0	13,0	8
	25	22,6	8,5	5		50	28,0	13,0	8
	30	22,0	8,5	5	55	28,0	13,0	8	
	35	22,0	8,5	5	60	28,0	13,0	8	
	40	22,0	8,5	5	65	28,0	13,0	8	
	45	22,0	8,5	5	70	28,0	13,0	8	
50	22,0	8,5	5	80	28,0	13,0	8		
55	22,0	8,5	5	90	28,0	13,0	8		
60	22,0	8,5	5	100	28,0	13,0	8		
M6	10	7,0	10,0	6	110	28,0	13,0	8	
	12	9,0	10,0	6	120	28,0	13,0	8	
	16	13,0	10,0	6	140	28,0	13,0	8	
	18	15,0	10,0	6	160	28,0	13,0	8	
	20	17,0	10,0	6	180	28,0	13,0	8	
	25	22,0	10,0	6	200	28,0	13,0	8	
	30	27,0	10,0	6	M10	16	11,5	16,0	10
	35	24,0	10,0	6		20	15,5	16,0	10
40	24,0	10,0	6	25		20,5	16,0	10	

d	L	b	D1	K	d	L	b	D1	K	d	L	b	D1	K
M10	30	25,5	16,0	10	M12	160	36,0	18,0	12	M20	60	52,5	30,0	20
	35	30,5	16,0	10		170	36,0	18,0	12		80	52,0	30,0	20
	40	35,5	16,0	10		180	36,0	18,0	12		100	52,0	30,0	20
	45	32,0	16,0	10		190	36,0	18,0	12		120	52,0	30,0	20
	50	32,0	16,0	10		200	36,0	18,0	12		140	52,0	30,0	20
	55	32,0	16,0	10		220	36,0	18,0	12		160	52,0	30,0	20
	60	32,0	16,0	10		240	36,0	18,0	12		180	52,0	30,0	20
	65	32,0	16,0	10		260	36,0	18,0	12		200	52,0	30,0	20
M10	70	32,0	16,0	10	M16	280	36,0	18,0	12	M24	220	52,0	30,0	20
	80	32,0	16,0	10		30	24,0	24,0	16		240	52,0	30,0	20
	90	32,0	16,0	10		35	29,0	24,0	16		260	52,0	30,0	20
	100	32,0	16,0	10		40	34,0	24,0	16		280	52,0	30,0	20
	110	32,0	16,0	10		45	39,0	24,0	16		300	52,0	30,0	20
	120	32,0	16,0	10		50	44,0	24,0	16		320	52,0	30,0	20
	130	32,0	16,0	10		55	49,0	24,0	16		340	52,0	30,0	20
	140	32,0	16,0	10		60	54,0	24,0	16		360	52,0	30,0	20
M12	150	32,0	16,0	10	65	44,0	24,0	16	400	52,0	30,0	20		
	170	32,0	16,0	10	70	44,0	24,0	16	M24	60	51,0	36,0	24	
	180	32,0	16,0	10	80	44,0	24,0	16		70	61,0	36,0	24	
	200	32,0	16,0	10	90	44,0	24,0	16		80	71,0	36,0	24	
	220	32,0	16,0	10	100	44,0	24,0	16		90	60,0	36,0	24	
	240	32,0	16,0	10	110	44,0	24,0	16		100	60,0	36,0	24	
	260	32,0	16,0	10	120	44,0	24,0	16		110	60,0	36,0	24	
	M12	20	14,8	18,0	12	130	44,0	24,0		16	120	60,0	36,0	24
25		19,8	18,0	12	M16	140	44,0	24,0		16	130	60,0	36,0	24
30		24,8	18,0	12		150	44,0	24,0	16	140	60,0	36,0	24	
35		29,8	18,0	12		160	44,0	24,0	16	150	60,0	36,0	24	
40		34,8	18,0	12		170	44,0	24,0	16	160	60,0	36,0	24	
45		39,8	18,0	12		180	44,0	24,0	16	170	60,0	36,0	24	
50		44,8	18,0	12		190	44,0	24,0	16	180	60,0	36,0	24	
55		36,0	18,0	12		200	44,0	24,0	16	200	60,0	36,0	24	
60	36,0	18,0	12	210		44,0	24,0	16	220	60,0	36,0	24		
M12	65	36,0	18,0	12	220	44,0	24,0	16	240	60,0	36,0	24		
	70	36,0	18,0	12	240	44,0	24,0	16	260	60,0	36,0	24		
	80	36,0	18,0	12	260	44,0	24,0	16	280	60,0	36,0	24		
	90	36,0	18,0	12	280	44,0	24,0	16	300	60,0	36,0	24		
	100	36,0	18,0	12	300	44,0	24,0	16	320	60,0	36,0	24		
	110	36,0	18,0	12	320	44,0	24,0	16	340	60,0	36,0	24		
	120	36,0	18,0	12	340	44,0	24,0	16	360	60,0	36,0	24		
	130	36,0	18,0	12	360	44,0	24,0	16	400	60,0	36,0	24		
140	36,0	18,0	12	400	44,0	24,0	16							
150	36,0	18,0	12	M20	50	42,5	30,0	20						