

Baying enclosure system VX25



System accessories Page 78

Material and surface finish:

- Enclosure frame: Sheet steel, 1.5 mm, dipcoat-primed and powder-coated, textured paint
- Roof: Sheet steel, 1.5 mm, dipcoat-primed and powder-coated, textured paint
- Door: Sheet steel, 2 mm, dipcoat-primed and powder-coated, textured paint
- Rear panel: Sheet steel, 1.5 mm, dipcoat-primed and powder-coated, textured paint
- Gland plate: Sheet steel, 1.5 mm, dipcoat-primed and powder-coated, textured paint
- Mounting plate: Sheet steel, 3 mm, zinc-plated

Colour:

- RAL 7035

Protection category IP to IEC 60 529:

- IP 66

NEMA protection category:


- NEMA 4

Supply includes:

- Enclosure frame
- Door (r/h hinge, may be swapped to opposite side)
- Roof plate
- Base
- Rear panel
- Mounting plate
- Lock: 3 mm double-bit
- 2 punched rails 18 x 39 mm

Approvals:

- UL
- cUL



IP 66/NEMA 4

Width (B) mm	P. of	800	Page
Height (H) mm		2000	
Depth (T) mm		600	
Mounting plate width (F) mm		699	
Mounting plate height (G) mm		1896	
Model No.	1 pc(s).	8807.000	
Accessories			
Base/plinth corner pieces with base/plinth trim panel, front and rear, 100 mm	2 pc(s).	8620.003	85
Base/plinth trim panels, sides, 100 mm	2 pc(s).	8620.033	86
Base/plinth corner pieces with base/plinth trim panel, front and rear, 200 mm	2 pc(s).	8620.023	85
Base/plinth trim panels, sides, 200 mm	2 pc(s).	8620.043	86
Levelling feet	4 pc(s).	4612.000	91
Side panels, screw-fastened, sheet steel	2 pc(s).	8106.245	96
Baying bracket, internal	6 pc(s).	8617.500	106
Baying block, internal	6 pc(s).	8617.501	106
Baying connector, external	6 pc(s).	8617.502	106
Comfort handle VX for lock inserts	1 pc(s).	8618.200	120
Comfort handle VX for semi-cylinder	1 pc(s).	8618.250	120
Wiring plan pocket, sheet steel, depth 35 mm	1 pc(s).	4118.500	127
Wiring plan pocket, sheet steel, depth 90 mm	1 pc(s).	4118.000	127
LED system light		see page	163
Cable duct		see page	186
Cable clamp rail, right angle section	2 pc(s).	8619.420	187