

Circuit-breaker component adaptors



Busbar system Page 212 Connection adaptors Page 216 Fuse elements Page 236

Material:

- Polyamide (PA 6.6)
- Fire protection corresponding to UL 94-V0

Colour:

- RAL 7035





Note:

- The technical data may vary for UL applications
- Cable outlet: Switch outlet or as outgoing cable from the switchgear

Technical details:

Available on the Internet

Rated current max. 100 – 125 A, 3-pole

						
Rated current max. A	Packs of	100	100	125	125	Page
Rated operating voltage V, ~		690, 3~	690, 3~	690, 3~	690, 3~	
Number of poles		3-pole	3-pole	3-pole	3-pole	
Cable outlet		Top	Bottom	Top	Bottom	
Type of connection		Box terminal	Box terminal	Box terminal	Box terminal	
Connection of round conductors mm ²		10 - 35	10 - 35	35 - 120	35 - 120	
Clamping area for laminated copper bars, W x H mm		10 x 7.8	10 x 7.8	18.5 x 15.5	18.5 x 15.5	
For switchgear make (model)		ABB (MS 497) Eaton (PKZ2) Schneider Electric (GV3ME80) Siemens (S3)	ABB (MS 497) Eaton (PKZ2) Schneider Electric (GV3ME80) Siemens (S3)	ABB (S2, T1, T1 UL, T2, T2 UL) Allen Bradley (140-CMN) Eaton (NZM1, NZM1 UL, BZM B1) GE (FD) OEZ (BC160N) Schneider Electric (NS80, NSC100, NSE75, NSE100) Siemens (3RV13 53, 3VT1) Terasaki (E125, S125)	ABB (S2, T1, T1 UL, T2, T2 UL) Allen Bradley (140-CMN) Eaton (NZM1, NZM1 UL, BZM B1) GE (FD) OEZ (BC160N) Schneider Electric (NS80, NSC100, NSE75, NS100) Siemens (3RV13 53, 3VT1) Terasaki (E125, S125)	
Width mm		72	72	90	90	
Height mm		210	210	225	225	
Approvals		UL	UL	UL	UL	
For bar systems with centre-to-centre spacing mm		60	60	60	60	
For bar thickness mm		5/10	5/10	5/10	5/10	
Model No.	1 pc(s).	9342.400	9342.410	9342.540	9342.550	
Product-specific supply scope						
Terminal cover		-	-	■	■	
Sliding blocks		-	-	■	■	
Accessories						
Support rails 35 x 15 mm	5 pc(s).	9320.120	9320.120	-	-	261
Sliding blocks	6 pc(s).	-	-	9342.560	9342.560	261
Connection bracket	3 pc(s).	-	-	9342.570	9342.570	261
Insert strip		-	-	-	-	