






Vertical Separator	
unassembled	301
assembled	311



Spacer*	
unassembled	305.08
assembled	315.08
unassembled	305.12
assembled	315.12



Strain Relief Separator	
unassembled	301.Z
assembled	311.Z




*For side-mounted applications


Option 1: Vertical Separators and Spacer for E-Chains®

Vertical Separators are used if a vertical subdivision of the E-Chain® interior is required - By standard Vertical Separators are assembled every other E-Chain® link


- **Standard** subdivision (Series 3400/Series 3500) with **Vertical Separator 311**, for combinations with **Full-Width Shelf 2210.X**
- If a broad distance shall be kept between the separators or they have to be fixed in their position, e.g. in case of side mounted applications, **Spacer 315.08** and **Spacer 315.12** can be used
- **Strain Relief Separator 301.Z**, integrable in the mounting bracket, to position at any point



Vert. Separator, slotted	
unassembled	302
assembled	312




Vert. Separator, slotted	
unassembled	302.24
assembled	312.24



Option 2: Full-Width Shelves for E-Chains®

For applications involving many thin cables with similar or identical diameters

- **Vertical Separator, slotted 312** and **Vertical Separator, slotted 312.24** (with wide base, e.g. in case of side mounted applications) - for applications with **Full-Width Shelf 321.X**




Full-Width Shelf	
X-1	
t = 3,4	


Width X [mm]	Part No. unassembled	Part No. assembled
050	320.050	321.050
075	320.075	321.075
100	320.100	321.100
115	320.115	321.115
125	320.125	321.125

Width X [mm]	Part No. unassembled	Part No. assembled
150	320.150	321.150
175	320.175	321.175
200	320.200	321.200
225	320.225	321.225
250	320.250	321.250


Side Plate	
unassembled	303
assembled	313



Middle Plate	
unassembled	304
assembled	314




Slotted Separator, open	
unassembled	307
assembled	317



Option 3: Shelves for E-Chains®

For applications involving many cables with different diameters. The Shelves can be arranged elevator-shifted with different bottoms within the entire E-Chain® width

- **Shelf 2210.X** can be combined with **Middle Plate 314** and **Side Plate 313**
- Option 3 "Shelves" can also be combined with option 1 "Vertical Separators"
- Assembling of the **Slotted Separator, open 317** in the existing separation afterwards possible



Shelf	
X	
X - 7	
t = 2,5	

Width X [mm]	Part No. unassembled	Part No. assembled
018	2200.18	2210.18
023	2200.23	2210.23
028	2200.28	2210.28
033	2200.33	2210.33
038	2200.38	2210.38
043	2200.43	2210.43
048	2200.48	2210.48

Width X [mm]	Part No. unassembled	Part No. assembled
058	2200.58	2210.58
068	2200.68	2210.68
073	2200.73	2210.73
088	2200.88	2210.88
099	2200.99	2210.99
124	2200.124	2210.124
149	2200.149	2210.149